



TO SNAP-LOCK INTO .187±.003
[4.75±0.08] HOLE, IN A .031 TO .078
[0.79 TO 1.98] THICK BOARD



.11 [2.8] REF.



"A"

.14 [3.6] REF.

TO SNAP-LOCK INTO .187±.003
[4.75±0.08] HOLE, IN A .062 [1.57]
THICK BOARD

- NOTES:
1. MATERIAL: NYLON 6/6 (RMS-01)
FLAME RETARDANT NYLON (RMS-19)
AVAILABLE BY SPECIAL ORDER ONLY
 2. COLOR: NATURAL

PART NO.	"A" ±.015
DLCBSRA3-6-01	3/8 [9.5]
DLCBSRA3-8-01	1/2 [12.7]
DLCBSRA3-10-01	5/8 [15.9]
DLCBSRA3-12-01	3/4 [19.1]
DLCBSRA3-14-01	7/8 [22.2]

TITLE: DUAL LOCKING CBS W/ RELEASABLE BOTTOM					DWG IN IN [MM]	
CREATED USING 1. UNLESS NOTED UNLESS NOTED XX±.010 XXX±.005 FRAC ±1/64 ANG ±1°					FINAL	PRINT TYPE
FILE # DLCBSRA3		DWN: S.J.	APP: S.J.	PART #		SEE TABLE CA
SHEET: 1 OF 1		SHEET SIZE: A	DT: 2.2.04	CHKD: DJZ		
RE: RICHCO		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060				
RE: --						
REV.	DESCRIPTION	ENGR.	DATE			
C	SEE CO 200435 FOR CHANGES	SK	09/11/09			
B	SEE ECN#840 FOR CHANGE DETAIL	SM	08/27/04			
A	RELEASED FOR PRODUCTION	SM	07/13/04			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[DLCBSRA3-10-01](#) [DLCBSRA3-12-01](#) [DLCBSRA3-14-01](#) [DLCBSRA3-6-01](#) [DLCBSRA3-8-01](#)