


REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	22/10/04	NJB
02	ECN 04-219	09/12/04	NJB
03	ECN 05-061	11/05/05	OW
04	ECN 06-253	24/11/06	OW
05	ECN 07-089	25/05/07	SF
06	CO-2010422	03/10/08	OW
07	CO-2010547	18/02/09	SF
08	CO-2010940	10/06/10	SF
09	CO-2010979	31/08/10	SF
10	CO-2011201	27/09/11	SF
11	CO-2011253	12/04/12	SF

NOTES:

- 1) ALL LENGTHS ARE AVAILABLE IN 1mm INCREMENTS.
- 2) PARTS AVAILABLE IN NYLON 6 GF25% V-0 (RMS-205), COLOUR NATURAL (MAY APPEAR BROWN) BY SPECIAL ORDER. TO ORDER ADD "V" TO THE END OF THE PART NUMBER. EXAMPLE: "HNSM2-20-5-1V"

ALTERNATE UNITS FOR REFERENCE ONLY

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT

RICHCO, INC. WWW.RICHCO-INC.COM		METRIC GENERAL TOLERANCES ± 0.25 ARE PRIMARY UNLESS OTHERWISE STATED 1 DECIMAL PLACE $\pm$ 2 DECIMAL PLACES $\pm$ ANGULAR $\pm 1^\circ$	
		IMPERIAL GENERAL TOLERANCES ± 0.010 ARE FOR REFERENCE UNLESS OTHERWISE STATED 1 DECIMAL PLACE $\pm$ 2 DECIMAL PLACES $\pm$ ANGULAR $\pm 1^\circ$	
MATERIAL: NYLON 6 25% GF (RMS-173)		COLOUR: BLACK (SEE NOTE 2)	
TITLE: HEXAGONAL THREADED SPACER, NYLON		PART No: HTSN-MD-L-H-1	
DRG No: 04-130	NPR REF: N/A		SIZE A4
DRN NJB	DATE 22/10/04	CHKD RC	DATE 23/10/04
SCALE NTS	SHEET No 1 OF 1		





FIG 1




FIG 2

PART NO.	D1=D2	H	L		FIG
HNSM2-L-5-1	M2	5[.197]	5-10[.197-.394]	11-45[.433-1.77]	2
HNSM2.5-L-5-1	M2.5		4-10[.158-.394]	11-55[.433-2.2]	2
HNSM3-L-5.5-1	M3	5.5[.22]	5-10[.197-.394]	16-65[.630-2.56]	1
HNSM3-L-6-1		6[.24]	5-15[.197-.591]	21-68[.827-2.678]	2
HNSM3-L-7-1		7[.276]	5-15[.197-.591]		
HNSM3-L-8-1		8[.32]	6-15[.237-.591]		
HNSM4-L-8-1	M4	10[.394]	5-20[.197-.788]	21-60[.827-2.363]	1
HNSM4-L-10-1			10-20[.394-.788]	21-65[.827-2.56]	2
HNSM5-L-10-1	M5	10[.394]	5-20[.197-.788]	21-60[.827-2.363]	
HNSM6-L-10-1	M6		10-20[.984-.788]	21-60[.827-2.363]	
		P1=P2	THROUGH	10[.394] MAX	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[HNSM3-13-5.5-1](#) [HNSM3-20-5.5-1](#) [HNSM3-30-5.5-1](#) [HTSN-M4-13-8-1](#) [HTSN-M4-20-8-1](#) [HTSN-M4-30-8-1](#)
[HNSM3-28-6-1](#)