




1




2

3



4



TYPE1



TYPE 2



TYPE 3


NOTES

- 1) METRIC PRIMARY UNITS: mm
IMPERIAL SECONDARY UNITS: [inches]
- 2) INSERT & STUD MATERIAL = BRASS(RMS-231) - NICKEL PLATING (RMS-229)
BODY MATERIAL = NYLON 6 - WHITE (RMS-133)
(Parts available in UL94-V0 material by special order)
- 3) UNTHREADED LENGTH = 1.5 PITCH MAX
- 4) ALL MATERIALS TO COMPLY TO RESTRICTION OF HAZARDOUS SUBSTANCES (RoHS) EUROPEAN UNION DIRECTIVE

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.

RICHCO, INC.
WWW.RICHCO-INC.COM

GENERAL TOLERANCES ±0.25 [0.010]
UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°



MATERIAL:		COLOUR:	
SEE NOTE 2		SEE NOTE 2	
DESCRIPTION:		PART No:	
MTNSP-MX-H-L-TYPE		SEE TABLE	
DRG No:		NPR No:	
3060070		N/A	
SHEET SIZE		A4	
DRN	DATE	CHKD	DATE
OW	28/06/05	NBr	28/06/05
SCALE	SHEET No.		
NTS	1 OF 1		

PART NUMBER	M	H	B	D	T	LENGTH(L)
MTNSP-M2.5-L-3	M2.5	6[.236]	6[.236]	-	-	4-12[.158-.472] (1mm INCREMENTS)
MTNSP-M2.5-L-2				4[.158]	.68[.027]	7-12[.276-.472] (1mm INCREMENTS)
MTNSP-M2.5-L-1			-			9-12[.354-.472] (1mm INCREMENTS)
MTNSP-M3-L-3	M3	7[.276]	6[.236]	-	-	4-12[.158-.472] (1mm INCREMENTS)
MTNSP-M3-L-2				4[.158]	.75[.030]	7-12[.276-.472] (1mm INCREMENTS)
MTNSP-M3-L-1			-			9-12[.354-.472] (1mm INCREMENTS)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[MTNSP-M3-10-2](#) [MTNSP-M3-10-1](#) [MTNSP-M3-10-3](#) [MTNSP-M3-11-1](#) [MTNSP-M3-11-2](#) [MTNSP-M3-11-3](#)