


NYLON 6/6 (RMS-01) PART NO.	NYLON 6/6 (RMS-19) PART NO.	"A" ±0.3 [±.012]	"B" ±0.2 [±.008]	"C" REF	"D" ±0.2 [±.008]	"E" ±0.2 [±.008]	"F" ±0.3 [±.012]	"L" ±0.3 [±.012]
PSD-4M-01	PSD-4M-19	4.0 [.157]	Ø2.5 [Ø.098]	4.2 [.165]	3.5 [.138]	6.0 [.236]	Ø7.0 [Ø.276]	9.35 [.368]
PSD-6M-01	PSD-6M-19	6.0 [.236]						11.35 [.447]
PSD-7M-01	PSD-7M-19	7.0 [.276]						12.35 [.486]
PSD-8M-01	PSD-8M-19	8.0 [.315]						13.35 [.526]
PSD-10M-01	PSD-10M-19	10.0 [.394]						15.35 [.604]
PSD-12M-01	PSD-12M-19	12.0 [.472]						17.35 [.683]
PSD-14M-01	PSD-14M-19	14.0 [.551]						19.35 [.762]
PSD-18M-01	PSD-18M-19	18.0 [.709]						23.35 [.919]



NOTES:
1,MATERIAL: SEE TABLE
2,COLOR: NATURAL
3,ALTERNATE UNITS FOR REFERENCE ONLY

B	SEE CO220069 FOR CHANGES	J.T 12.01.10
A	RELEASED FOR PRODUCTION	J.T 02.24.10
R E V.	DESCRIPTION	ENGR. DATE

TITLE:

PUSH SPACER



CREATED USING SOLIDWORKS	FILE #: PSD		DWN: J.T	APP: J.T	FINAL	
TOLERANCES UNLESS NOTED	SHEET: 1 OF 1	SHEET SIZE: A	DT: 07.14.09	CHKD: -	PART #	PRINT TYPE
DIM ±: SEE TABLE ANG. ±1°	RE: RICHCO --		RICHCO WWW.RICHCO-INC.COM (+86) 592-6884500		SEE TABLE	CA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[PSD-8M-01](#) [PSD-10M-01](#) [PSD-10M-19](#) [PSD-12M-01](#) [PSD-12M-19](#) [PSD-14M-01](#) [PSD-14M-19](#) [PSD-7M-01](#) [PSD-7M-19](#) [PSD-8M-19](#) [PSD-18M-01](#) [PSD-18M-19](#) [PSD-4M-01](#) [PSD-4M-19](#) [PSD-6M-01](#) [PSD-6M-19](#)