


	PART NO.	DIM "A" ±.015(0.4)	STUD LENGTH
	SFCBS-M4-10M-01	.39 (10)	.31 (8)
	SFCBS-M4-12M-01	.47 (12)	.39 (10)
	SFCBS-M4-14M-01	.55 (14)	.47 (12)
	SFCBS-M4-16M-01	.63 (16)	.55 (14)
	SFCBS-M4-18M-01	.71 (18)	.63 (16)
	SFCBS-M4-20M-01	.79 (20)	.71 (18)



NOTES:

1. MATERIAL: NYLON 6/6 UL94 V-2 (RMS-01).
-NYLON 6/6 UL94 V-0 (RMS-19),
AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER REPLACE "-01" WITH "-19"
2. COLOR: NATURAL

TITLE: STUD-FITTING CIRCUIT BOARD SUPPORT				DWG IN IN (MM)	
				FINAL	
TOLERANCES UNLESS NOTED		FILE # SFCBS	DWN: J.B.	APP:	
.XX=±.010		MAT'L: SEE NOTES	DT: 05-31-96	DT:	
.XXX=±.005		RE: RICHCO, INC.	PART #		
FRAC=±1/64		SEE TABLE			PRINT
ANG=±1°		(773) 539-4060			TYPE
					CA
SEE CO 200407 FOR CHANGES	SK 08.04.09				
SEE CO 200404 FOR CHANGES	SK 07.31.09				
CHANGED FILE NO.AND TITLE BLOCK	SM 05.10.01				
REV	DESCRIPTION	ENGR	DATE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

[SFCBS-M4-10M-01](#) [SFCBS-M4-12M-01](#) [SFCBS-M4-14M-01](#) [SFCBS-M4-16M-01](#) [SFCBS-M4-18M-01](#) [SFCBS-M4-20M-01](#)