







Part No	Hole Dia	Panel Thickness	Head Dia.	Head Thickness	Length
XT1250125A	.125 (3.2)	.062-.125 (1.6-3.2)	.344 (8.7)	.062 (1.6)	.208 (5.3)
XT1250250A	.125 (3.2)	.062-.250 (1.6-6.4)	.344 (8.7)	.062 (1.6)	.321 (8.2)
XT1250375A	.125 (3.2)	.062-.375 (1.6-9.5)	.344 (8.7)	.062 (1.6)	.458 (11.6)
XT1880250A	.188 (4.8)	.062-.250 (1.6-6.4)	.500 (12.7)	.078 (2.0)	.348 (8.8)
XT1880375A	.188 (4.8)	.062-.375 (1.6-9.5)	.500 (12.7)	.078 (2.0)	0.473(12.0)
XT1880500A	.188 (4.8)	.062-.500 (1.6-12.7)	.500 (12.7)	.078 (2.0)	.598 (15.2)
XT1880625A	.188 (4.8)	.062-.625 (1.6-15.9)	.500 (12.7)	.078 (2.0)	.723 (18.4)
XT1880750A	.188 (4.8)	.062-.750 (1.6-19.1)	.500 (12.7)	.078 (2.0)	.848 (21.5)
XT2500250A	.250 (6.4)	.062-.250 (1.6-6.4)	.700 (17.8)	.1 (2.5)	.391 (9.9)
XT2500375A	.250 (6.4)	.062-.375 (1.6-9.5)	.700 (17.8)	.1 (2.5)	.506 (12.9)
XT2500500A	.250 (6.4)	.062-.500 (1.6-12.7)	.700 (17.8)	.1 (2.5)	.630 (16)
XT2500625A	.250 (6.4)	.062-.625 (1.6-15.9)	.700 (17.8)	.1 (2.5)	.755 (19.2)
XT2500750A	.250 (6.4)	.062-.750 (1.6-19.1)	.700 (17.8)	.1 (2.5)	.880 (22.4)
XT2500875A	.250 (6.4)	.062-.875 (1.6-22.2)	.700 (17.8)	.1 (2.5)	1.00 (25.5)
XT2501000A	.250 (6.4)	.062-1.00 (1.6-25.4)	.700 (17.8)	.1 (2.5)	1.12 (28.5)
XT2501250A	.250 (6.4)	.062-1.25 (1.6-31.8)	.700 (17.8)	.1 (2.5)	1.38 (35.1)
XT2501500A	.250 (6.4)	.062-1.25 (1.6-38.1)	.700 (17.8)	.1 (2.5)	1.63 (41.5)
XT2501750A	.250 (6.4)	.062-1.75 (1.6-44.5)	.700 (17.8)	.1 (2.5)	1.88 (47.8)
XT2502000A	.250 (6.4)	.062-2.00 (1.6-50.8)	.700 (17.8)	.1 (2.5)	2.13 (54.2)
XT2810250A	.281 (7.1)	.062-.250 (1.6-6.4)	.787 (20.0)	.1 (2.5)	.384 (9.8)
XT2810375A	.281 (7.1)	.062-.375 (1.6-9.5)	.787 (20.0)	.1 (2.5)	.515 (13.1)
XT2810500A	.281 (7.1)	.062-.500 (1.6-12.7)	.787 (20.0)	.1 (2.5)	.642 (16.3)
XT2810625A	.281 (7.1)	.062-.625 (1.6-15.9)	.787 (20.0)	.1 (2.5)	.767 (19.5)
XT2810750A	.281 (7.1)	.062-.750 (1.6-19.1)	.787 (20.0)	.1 (2.5)	.894 (22.7)
XT2810875A	.281 (7.1)	.062-.875 (1.6-22.2)	.787 (20.0)	.1 (2.5)	1.02 (25.9)
XT2811000A	.281 (7.1)	.062-1.00 (1.6-25.4)	.787 (20.0)	.1 (2.5)	1.15 (29.1)
XT2811250A	.281 (7.1)	.062-1.25 (1.6-31.8)	.787 (20.0)	.1 (2.5)	1.40 (35.6)
XT2811500A	.281 (7.1)	.062-1.25 (1.6-38.1)	.787 (20.0)	.1 (2.5)	1.65 (41.9)
XT2811750A	.281 (7.1)	.062-1.75 (1.6-44.5)	.787 (20.0)	.1 (2.5)	1.90 (48.3)
XT2812000A	.281 (7.1)	.062-2.00 (1.6-50.8)	.787 (20.0)	.1 (2.5)	2.15 (54.6)
XT3120250A	.312 (7.9)	.062-.250 (1.6-6.4)	.874 (22.2)	.1 (2.5)	.410 (10.4)
XT3120375A	.312 (7.9)	.062-.375 (1.6-9.5)	.874 (22.2)	.1 (2.5)	.529 (13.4)
XT3120500A	.312 (7.9)	.062-.500 (1.6-12.7)	.874 (22.2)	.1 (2.5)	.642 (16.3)
XT3120625A	.312 (7.9)	.062-.625 (1.6-15.9)	.874 (22.2)	.1 (2.5)	.783 (19.9)
XT3120750A	.312 (7.9)	.062-.750 (1.6-19.1)	.874 (22.2)	.1 (2.5)	.894 (22.7)
XT3120875A	.312 (7.9)	.062-.875 (1.6-22.2)	.874 (22.2)	.1 (2.5)	1.04 (26.3)
XT3121000A	.312 (7.9)	.062-1.00 (1.6-25.4)	.874 (22.2)	.1 (2.5)	1.16 (29.5)
XT3121250A	.312 (7.9)	.062-1.25 (1.6-31.8)	.874 (22.2)	.1 (2.5)	1.42 (36)
XT3121500A	.312 (7.9)	.062-1.25 (1.6-38.1)	.874 (22.2)	.1 (2.5)	1.67 (42.4)
XT3121750A	.312 (7.9)	.062-1.75 (1.6-44.5)	.874 (22.2)	.1 (2.5)	1.93 (49.0)
XT3122000A	.312 (7.9)	.062-2.00 (1.6-50.8)	.874 (22.2)	.1 (2.5)	2.18 (55.5)
XT3750250A	.375 (9.5)	.062-.250 (1.6-6.4)	1.00 (22.4)	.1 (2.5)	.445 (11.3)
XT3750375A	.375 (9.5)	.062-.375 (1.6-9.5)	1.00 (22.4)	.1 (2.5)	.570 (14.5)
XT3750500A	.375 (9.5)	.062-.500 (1.6-12.7)	1.00 (22.4)	.1 (2.5)	.689 (17.5)
XT3750625A	.375 (9.5)	.062-.625 (1.6-15.9)	1.00 (22.4)	.1 (2.5)	.816 (20.7)
XT3750750A	.375 (9.5)	.062-.750 (1.6-19.1)	1.00 (22.4)	.1 (2.5)	.943 (24)
XT3750875A	.375 (9.5)	.062-.875 (1.6-22.2)	1.00 (22.4)	.1 (2.5)	1.07 (27.2)
XT3751000	.375 (9.5)	.062-1.00 (1.6-25.4)	1.00 (22.4)	.1 (2.5)	1.196 (30.4)
XT3751250A	.375 (9.5)	.062-1.25 (1.6-31.8)	1.00 (22.4)	.1 (2.5)	1.45 (36)
XT3751500A	.375 (9.5)	.062-1.25 (1.6-38.1)	1.00 (22.4)	.1 (2.5)	1.71 (43.3)
XT3751750A	.375 (9.5)	.062-1.75 (1.6-44.5)	1.00 (22.4)	.1 (2.5)	1.96 (49.8)
XT3752000A	.375 (9.5)	.062-2.00 (1.6-50.8)	1.00 (22.4)	.1 (2.5)	2.21 (56.2)

NOTES:
1. MATERIAL: NYLON 6/6 ZR207
2. COLOR: BLACK

A	RELEASED FOR PRODUCTION	MJB 10/16/2014
REV.	DESCRIPTION	ENGR. DATE

TITLE: XT SERIES XMAS TREE CLIP FASTENER		UNITS: IN [MM]	
CREATED USING SOLIDWORKS	FILE #: XT SERIES	DWN: M.J.B.	APP: -
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: B	DT: 11/21/13
RE:		CHKD: -	FINAL
PART #		PRINT TYPE	
SEE TABLE		CA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Essentra:

<u>XT1880625A</u>	<u>XT1250125A</u>	<u>XT2500500A</u>	<u>XT3752000A</u>	<u>XT2502000A</u>	<u>XT2811750A</u>	<u>XT2500625A</u>	<u>XT3751500A</u>
<u>XT2501250A</u>	<u>XT3750500A</u>	<u>XT2500250A</u>	<u>XT2811000A</u>	<u>XT2811250A</u>	<u>XT2810625A</u>	<u>XT1880500A</u>	<u>XT3750375A</u>
<u>XT2810750A</u>	<u>XT2810875A</u>	<u>XT3751250A</u>	<u>XT1880250A</u>	<u>XT2501750A</u>	<u>XT3750875A</u>	<u>XT1250250A</u>	<u>XT2500750A</u>
<u>XT3750250A</u>	<u>XT1880750A</u>	<u>XT3750625A</u>	<u>XT2500875A</u>	<u>XT2811500A</u>	<u>XT2501500A</u>	<u>XT2501000A</u>	<u>XT3751000A</u>
<u>XT3751750A</u>	<u>XT2810375A</u>	<u>XT2810250A</u>	<u>XT1250375A</u>	<u>XT2812000A</u>	<u>XT2500375A</u>	<u>XT3750750A</u>	<u>XT2810500A</u>
<u>XT1880375A</u>							