



PART NO.	MAX. BUNDLE DIA.	"L" LENGTH REF	"W" WIDTH REF.	"T" THICKNESS REF.	"A" REF	"B" REF	MIN. LOOP TENSILE
WITA-F1-18R-M	.87 (22)	3.98 (100)	.10 (2.5)	.039 (1)	1 (25.4)	.31 (7.9)	18 LBS.
WITA-F2-18R-M	.98 (25)	4.33 (110)					



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
2. COLOR: NATURAL.
3. MATERIAL: UV STABILIZED (RMS-46),
COLOR: BLACK, AVAILABLE BY SPECIAL ORDER ONLY.
TO ORDER ADD SUFFIX "-UVB" TO PART NO.
4. SUFFIX "-M" IS FOR PACKAGING OF 1000 PCS.

TITLE: MARKER FLAG TIES			DWG IN IN (mm)		FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°			FILE # WITA-F	DWN: D.K.	DT:05/27/10	PART #
RE: RICHCO, INC.			MAT'L: SEE NOTES	CHKD:D.Z.	ENG:D.K.	SEE TABLE
B ADDED NOTE 4. SEE CO 200661 DK 05.12.11			RICHCO INC. ENG@RICHCO-INC.COM (773) 539-4060			PRINT TYPE CA
A RELEASED FOR PRODUCTION, CO 200524 DK 05.27.10						
REV DESCRIPTION ENGR DATE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[WITA-F1-18R-M](#)