Toggle

Switches







| SERIES | FEATURE | ACTUATION | MAX RATING (Resistive @ 28VDC) | SEAL RATING | MOUNTING | CIRCUITRY |
|--------|--|--------------------------|--------------------------------------|---|----------------------------|-----------------------------|
| T1 | 2 or 3 Position, 1 to 8 Poles, Lever Lock Option | Momentary, Maintained | 8A | MIL-PRF-83731 | 15/32"or 7/16" Threaded | Multi-Pole B2, B3 Basics |
| T3 | Snap Action, Lever Lock Option | Momentary, Maintained | 5A | MIL-PRF-83731 - 15/32" Threaded Only | 15/32" or 1/4" Threaded | SPST, DPST |
| T7 | Lower Cost, Sealed | Momentary, Maintained | 16A | IP68S & IP69K | 15/32" Threaded | SPST, SPDT DPST, DPDT |
| T71 | Thinner T7 Sealed | Momentary, Maintained | 16A | IP68S & IP69K | 15/32" Threaded | SPST, SPDT |
| Т9 | High Performance Lever Lock Option | Momentary, Maintained | 20A | IP68S or MIL-DTL-3950 | 15/32" Threaded | SPST, SPDT DPST, DPDT |
| TE | Snap Action, Non-Teasible | Momentary, Maintained | 5A | MIL-DTL-8834 | 15/32" or 1/4" Threaded | SPST, DPST |