

Cable to Board (Rear Panel Mount)

.050"

9 thru 100 Contacts

Rugged Board Mount

MK


Rugged Cable

MM, MN

MM-212-031-161-41WQ
(METAL)

MN-211-031-161-41WQ
(PLASTIC)

MK-2C2-031-235-2600
(METAL)



DIMENSIONS															
SIZE	CONTACT ROWS	A	B		C	D	E	H	HARDWARE	J	K	L	M	N	
			PLUG MAX	RCPT MAX			POTTING WELL MAX								
9	2	.775	.334	.400	.390	.565	.270	.298	#2-56 UNC THD	.957	.480	.773	.298	.210	
15		.925	.484	.550	.540	.715				1.107		.923			
21		1.075	.634	.700	.690	.865				1.257		1.073			
25		1.175	.734	.800	.790	.965				1.357		1.173			
31		1.325	.884	.950	.940	1.115				1.507		1.323			
37	3	1.475	1.034	1.100	1.090	1.265	.310	.341	#2-56 UNC THD	1.657	.523	1.477	.440	.239	
51		1.425	.984	1.050	1.040	1.215				1.657		1.777			
69*		1.725	1.284	1.350	1.340	1.515				1.957					
100	4	2.160	1.384	1.508	1.432	1.800	.360	.384	#4-40 UNC THD	2.383	.600	2.219	.515	.301	

* = 69 POSITION CONNECTORS ARE AVAILABLE IN METAL ONLY.

** = SHELL ACCEPTS .200 MAX #2-56 SCREW LENGTH (.295 MAX #4-40 SCREW LENGTH).