

PLUG/RECEPTACLE: MQ- 212 - 031 - 143 - 2200 - 93A  
 MP- 211 - 031 - 143 - 2200 - 93A  
 XX-XXX-XXX-XXX-XXXX-XXX

## SERIES

MQ .050" Low Profile Metal  
 MP .050" Low Profile Plastic

## BODY

- 2 2-Row (Sizes 9 thru 37)
- 3 3-Row (Size 51)

### BODY STYLE:

- 1 Plug/Receptacle, straight with mounting ears

### BODY MATERIAL:

- 1 Polyphenylene Sulfide (MN only)
- 2 Polyphenylene Sulfide with electroless nickel shell
- 3 Polyphenylene Sulfide with electrodeposited cadmium shell ☒
- 4 Polyphenylene Sulfide with hard anodized back shell

## SIZE

XXX 009, 015, 021, 025, 031, 037, 051

## CONTACTS

### TYPE CONTACTS/TERMINATIONS:

- 14 Pin/Socket, straight

### PLATING OPTIONS:

- 3 50  $\mu$ " Au contacts: 10  $\mu$ " Au terminations

## HARDWARE

### STYLE OF HARDWARE:

- 00 None
- 22 Two fixed jacknut assemblies
- JA Turning jackpost with retaining ring, uninstalled
- JP Turning jackpost, internal thread on plug side
- JS Turning jackpost, internal thread on receptacle side

### POLARIZATION / WIRING:

- 00 None

## SPECIAL DESIGNATORS

93A Connector saver designator

☒ = Option not RoHS compliant

