


REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	08/18/14	J. C.
B	Engineering Update w/o Changes	08/11/16	J. C.



- NOTES:
1. SEALED TO IP54 RATING
 2. VOLTAGE INPUT OPTIONS: 12V/24V/110V/220V
 3. ROHS COMPLIANT
 4. MOUNTING HARDWARE PACKED SEPARATELY NON-ASSEMBLED
 5. INSERT SEALING RING ON PANEL MOUNT ASSEMBLY PRIOR TO PANEL INSTALLATION

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		
.XX ± .02			
.XXX ± .010		TITLE: MPR8-3 SERIES, IP54 RATED PANEL MOUNT INDICATOR	
DESIGNED: M. Doan	DATE: 08/18/14	PART NO: MPR8-3XDXXV	REVISION: B
CHECKED: B. Oliver	DATE: 08/18/14	CAGE CODE : 32559	SHEET # 1 OF 2
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET #1		

Part Number	Dominant Wave Length λ_d (nm)	Emitted Color	Lens Appearance	Voltage	Luminous Intensity (mcd)	Viewing Angle (degree)
MPR8-3RD12V	625	Red	Diffused	12V	310	45
MPR8-3GD12V	515	Green	Diffused	12V	2090	45
MPR8-3YD12V	590	Yellow	Diffused	12V	310	45
MPR8-3BWD12V	470	Blue	Diffused	12V	625	45
MPR8-3WD12V	x=0.36, y=0.32	White	Diffused	12V	4910	45
MPR8-3RD24V	625	Red	Diffused	24V	310	45
MPR8-3GD24V	515	Green	Diffused	24V	2090	45
MPR8-3YD24V	590	Yellow	Diffused	24V	310	45
MPR8-3BWD24V	470	Blue	Diffused	24V	625	45
MPR8-3WD24V	x=0.36, y=0.32	White	Diffused	24V	4910	45
MPR8-3RD110V	625	Red	Diffused	110V	20	45
MPR8-3GD110V	515	Green	Diffused	110V	125	45
MPR8-3YD110V	590	Yellow	Diffused	110V	20	45
MPR8-3BWD110V	470	Blue	Diffused	110V	40	45
MPR8-3WD110V	x=0.36, y=0.32	White	Diffused	110V	165	45
MPR8-3RD220V	625	Red	Diffused	220V	10	45
MPR8-3GD220V	515	Green	Diffused	220V	60	45
MPR8-3YD220V	590	Yellow	Diffused	220V	10	45
MPR8-3BWD220V	470	Blue	Diffused	220V	20	45
MPR8-3WD220V	x=0.36, y=0.32	White	Diffused	220V	80	45

ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)

POWER INPUT _____ 0.5W MAX

OPERATING TEMPERATURE RANGE _____ -40°C ~ 80°C

STORAGE TEMPERATURE _____ -40°C ~ 80°C

TERMINAL SOLDERING TEMPERATURE _____ 260°C, 5s

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) <u>DECIMALS</u> <u>ANGULAR</u>		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
		TITLE: MPR8-3 SERIES, IP54 RATED PANEL MOUNT INDICATOR	
DESIGNED: M. Doan	DATE: 08/18/14	PART NO: MPR8-3XDXXV	REVISION: B
CHECKED: B. Oliver	DATE: 08/18/14	CAGE CODE : 32559	SHEET # 2 OF 2
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			