

Specification Sheet

Part Number: ATS10266110



Available in reels of 1640 feet for extended use before refilling.

Cable Ties for ATS Systems, 50lb Tensile Strength, PA66HIRHSUV, Black, 1640 ft/reel

Article Number	102-66110
Type	Strap_Black_ATS
Color	Black (BK)
Quantity Per	pack
Product Description	The cable tie strap for the ATS Flex is designed for optimized material utilization. This innovative two-piece system consists of a separate strap and closure, eliminating waste and the associated jobsite cleanup.
Short Description	Cable Ties for ATS Systems, 50lb Tensile Strength, PA66HIRHSUV, Black, 1640 ft/reel
Global Part Name	Strap_Black_ATS-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	1640.0
Length L (Metric)	500.0
Identification Plate Position	none
Reel Diameter (Imperial)	15.25
Reel Diameter (Metric))	387
Reel Width (Imperial)	3.5
Reel Width (Metric)	88.9
Releasable Closure	No
Variant	on reel
Width W (Imperial)	0.18
Width W (Metric)	4.5
Bundle Diameter Min (Metric)	0.0
Bundle Diameter Max (Imperial)	3.94
Bundle Diameter Max (Metric)	100

Height H (Imperial)	0.047
Height H (Metric)	1.2
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1640
Package Quantity (Metric)	500
Customs Number	3926909988

Reel Weight (Imperial)	6
Reel Weight (Metric)	2.72

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)