

Specification Sheet


Part Number: 109-00010

Open-head design with easily detectable slot opening allows for swift and easy insertion

Pre-lock feature allows for a temporary hold

The large ribbed tail permits an ergonomic installation

Two rails on the strap ensure guidance through the cable tie head



Q Tie, 6.3" Long, 30lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	109-00010
----------------	-----------

Type	Q30R
------	------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Q-Ties have a distinctive open-style head, a pre-lock function, and a large ribbed tail. The easily detectable slot opening offered with the tail and tie head provides ease of placement when working with gloves or for blind applications with limited view of the installation. The pre-lock feature allows for temporary holding of cable and wire bundles, permitting additional cables and wires to be placed without destroying the cable tie. Q-Ties can be tensioned by hand or with one of HellermannTyton's mechanical cable tie application tools.
---------------------	---

Short Description	Q Tie, 6.3" Long, 30lb Tensile Strength, PA66, Natural, 100/pkg
Global Part Name	Q30R-PA66-NA
Minimum Tensile Strength (Imperial)	30
Minimum Tensile Strength (Metric)	130
Length L (Imperial)	6.3
Length L (Metric)	160.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.12
Bundle Diameter Min (Metric)	3.0
Bundle Diameter Max (Imperial)	1.5
Bundle Diameter Max (Metric)	38.0

Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 62275 UL ANSI/UL 1565
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100

Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)