

Specification Sheet

Part Number: T250XL9X2



- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.

Heavy Duty Cable Tie, 41" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Article Number	111-00466
Type	T250XL
Color	Natural (NA)
Quantity Per	pack
Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 41" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Global Part Name	T250XL-PA66-NA
------------------	----------------

Minimum Tensile Strength (Imperial)	250
-------------------------------------	-----

Minimum Tensile Strength (Metric)	1115
-----------------------------------	------

Length L (Imperial)	41.0
---------------------	------

Length L (Metric)	1030.0
-------------------	--------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.49
--------------------	------

Width W (Metric)	12.4
------------------	------

Bundle Diameter Min (Imperial)	0.47
--------------------------------	------

Bundle Diameter Min (Metric)	12.0
------------------------------	------

Bundle Diameter Max (Imperial)	12.01
--------------------------------	-------

Bundle Diameter Max (Metric)	305.0
------------------------------	-------

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 1565 UL ANSI/UL 746B UL ANSI/UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)