

Specification Sheet

Part Number: T30L9C2



- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.

Cable Tie, 8" Long, UL Rated, 30lb Tensile Strength, PA66, Natural, 100/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                              |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 111-03325                                                                                                                                                                                                                                                                                                                                                    |
| Type                | T30L                                                                                                                                                                                                                                                                                                                                                         |
| Color               | Natural (NA)                                                                                                                                                                                                                                                                                                                                                 |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                                         |
| Product Description | T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. |
| Short Description   | Cable Tie, 8" Long, UL Rated, 30lb Tensile Strength, PA66, Natural, 100/pkg                                                                                                                                                                                                                                                                                  |

|                                     |                 |
|-------------------------------------|-----------------|
| Global Part Name                    | T30L-PA66-NA    |
| Minimum Tensile Strength (Imperial) | 30              |
| Minimum Tensile Strength (Metric)   | 135             |
| Length L (Imperial)                 | 7.80            |
| Length L (Metric)                   | 198.0           |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.14            |
| Width W (Metric)                    | 3.6             |
| Bundle Diameter Min (Imperial)      | 0.06            |
| Bundle Diameter Min (Metric)        | 1.5             |
| Bundle Diameter Max (Imperial)      | 1.97            |
| Bundle Diameter Max (Metric)        | 50.0            |

|                               |                                  |
|-------------------------------|----------------------------------|
| Material                      | Polyamide 6.6 (PA66)             |
| Material Shortcut             | PA66                             |
| Flammability                  | UL 94 V-2                        |
| Halogen Free                  | Yes                              |
| UV Resistant (Yes/No)         | No                               |
| Use Conditions                | For Indoor Use Only              |
| Plenum Rating                 | AH-2                             |
| Operating Temperature         | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33)  | Yes                              |
| ROHS Compliant                | Yes                              |
| Certification/Specification   | UL 62275                         |
| UL Recognized (US)            | Yes                              |
| UL Listed (US and Canada)     | Yes                              |
| UL Recognized (US and Canada) | Yes                              |
| UL Listed (US)                | Yes                              |
| Package Quantity (Imperial)   | 100                              |

|                           |            |
|---------------------------|------------|
| Package Quantity (Metric) | 100        |
| Customs Number            | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)