

Specification Sheet

Part Number: T120L0UVK2



UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.

Inside serrations allow for strong grip on cables and wire bundles.

Head design provides high tensile strength with very low insertion force.

Heavy Duty Cable Tie, 30" Long, UL Rated, 120lb Tensile Strength, PA66UV, Black, 50/pkg

Article Number	111-12460
Type	T120L
Color	Black (BK)
Quantity Per	pack
Product Description	Used in the solar industry and other applications, HellermannTyton offers cable ties made of UV stabilized PA66UV material. This material provides additional protection against UV radiation for long-term outdoor use and is available in various styles, tensile strengths, and bundle diameters. T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Heavy Duty Cable Tie, 30" Long, UL Rated, 120lb Tensile Strength, PA66UV, Black, 50/pkg
Global Part Name	T120L-PA66UV-BK
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	30.0
Length L (Metric)	760.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.2
Bundle Diameter Min (Metric)	5.0
Bundle Diameter Max (Imperial)	8.86
Bundle Diameter Max (Metric)	225.0

Thickness T (Imperial) 0.075

Thickness T (Metric) 1.9

Cable Tie Head Length (Imperial) 0.39

Cable Tie Head Width (Imperial) 0.51

Height H (Metric) 7.8

Material Polyamide 6.6 UV-resistant (PA66UV)

Material Shortcut PA66UV

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) Yes

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Certification/Specification CAGE Code 53421 UL | csa-C22.2 no. 62275 VG 95387 Part 4

UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)