

Specification Sheet

Part Number: 111-12761



- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serrations produce strong grip on cables and wire bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail ensures a quick and simple installation.

Cable Tie, 21" Long, 120lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	111-12761
Type	T120X
Color	Natural (NA)
Quantity Per	pack
Product Description	Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 21" Long, 120lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name	T120X-PA66-NA
------------------	---------------

Minimum Tensile Strength (Imperial)	120
-------------------------------------	-----

Minimum Tensile Strength (Metric)	535
-----------------------------------	-----

Length L (Imperial)	21.0
---------------------	------

Length L (Metric)	530.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.30
--------------------	------

Width W (Metric)	7.6
------------------	-----

Bundle Diameter Min (Imperial)	0.19
--------------------------------	------

Bundle Diameter Min (Metric)	4.8
------------------------------	-----

Bundle Diameter Max (Imperial)	5.94
--------------------------------	------

Bundle Diameter Max (Metric)	151
------------------------------	-----

Thickness T (Imperial)	0.07
------------------------	------

Thickness T (Metric)	1.9
----------------------	-----

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com