

Specification Sheet

Part Number: T150XLL4X2



- Engineered and manufactured for maximum performance and quality
- Made from 100% high-quality plastic to ensure efficient recycling
- Inside serration for a strong grip onto bundles
- Easy application either manually or with a processing tool

Heavy Duty Cable Tie, 52" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg

Article Number	111-15302
Type	T150XLL
Color	Yellow (YE)
Quantity Per	pack
Product Description	HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are availableto ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 52" Long, UL Rated, 175lb Tensile Strength, PA66, Yellow, 25/pkg
Global Part Name	T150XLL-PA66-YE

Minimum Tensile Strength (Imperial)	175
Minimum Tensile Strength (Metric)	780
Length L (Imperial)	52.0
Length L (Metric)	1325.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.9
Bundle Diameter Min (Imperial)	5.98
Bundle Diameter Min (Metric)	152.0
Bundle Diameter Max (Imperial)	15.94
Bundle Diameter Max (Metric)	405.0
Material	Polyamide 6.6 (PA66)

Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 UL ANSI/UL 746B UL ANSI/UL 1565
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)