

Specification Sheet

Part Number: TELS-SPK2



Continuous strap and separate heads allow for any bundle diameter, eliminating waste.

Smooth strap prevents cable damage.

Extended-Length Tie Spacer, PP, Black, 50/pkg

Article Number	111-32000
Type	EL-TY (TELS-SPK2)
Color	Black (BK)
Quantity Per	pack
Product Description	Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.
Short Description	Extended-Length Tie Spacer, PP, Black, 50/pkg

Global Part Name	EL-TY (TELS-SPK2)-PP-BK
------------------	-------------------------

Contents of pkg/kit	50 Spacer
---------------------	-----------

Minimum Tensile Strength (Imperial)	250
-------------------------------------	-----

Minimum Tensile Strength (Metric)	1115
-----------------------------------	------

Length L (Imperial)	1.2
---------------------	-----

Length L (Metric)	30.5
-------------------	------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	steel pawl
-------------	------------

Variant	Endless
---------	---------

Width W (Imperial)	2.1
--------------------	-----

Width W (Metric)	53.3
------------------	------

Height H (Imperial)	0.67
---------------------	------

Height H (Metric)	17.0
-------------------	------

Cable Tie Width Max (Imperial)	0.5
--------------------------------	-----

Cable Tie Width Max (Metric)	12.7
------------------------------	------

Material	Polypropylene (PP)
Material Shortcut	PP
Material Head	Polyacetal, UV stabilized (POMUV) with stainless steel pawl (SS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)