

Specification Sheet

Part Number: 115-07190



Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: strong, yet elastic, and suitable for temperatures as low as -20 degrees C.

The SOFTFIX ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres etc.

Cable Tie without Serration, 7" Long, Flexible TPU, Black, 16/pkg

Article Number	115-07190
----------------	-----------

Type	SOFTFIX XS
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Soft, flexible material makes these ties particularly suitable for use on sensitive wires, such as fibre-optic cables. Additionally the ties are suitable for use on moving or vibrating applications. The double slotted head allows for parallel bundling.
---------------------	--

Short Description	Cable Tie without Serration, 7" Long, Flexible TPU, Black, 16/pkg
-------------------	---

Global Part Name	SOFTFIX XS-TPU-BK
------------------	-------------------

Minimum Tensile Strength (Metric)	57
Length L (Imperial)	7.0
Length L (Metric)	180
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	ladder style
Variant	Not Serrated
Width W (Metric)	7.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Thickness T (Metric)	1.7
Material	Thermoplastic Polyurethane (TPU)

Material Shortcut	TPU
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	16
Package Quantity (Metric)	16
Customs Number	3926909988
Weight (Metric)	0.04

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com