

Specification Sheet

Part Number: RT255R0HIRX2



High impact, heat and UV stabilized releasable cable ties contain an impact modifier allowing greater flexibility and greater resistance to vibration.

Special design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Releasable Cable Tie, Release Tab, 20" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Article Number	115-01300
Type	RT255R
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton heavy duty releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Releasable Cable Tie, Release Tab, 20" Long, 250lb Tensile Strength, PA66HIRHSUV, Black, 25/pkg

Global Part Name	RT255R-PA66HIRHSUV-BK
------------------	-----------------------

Minimum Tensile Strength (Imperial)	250
-------------------------------------	-----

Minimum Tensile Strength (Metric)	1115
-----------------------------------	------

Length L (Imperial)	20.0
---------------------	------

Length L (Metric)	508.0
-------------------	-------

Fixation Method	Releasable Cable Tie
-----------------	----------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	Yes
--------------------	-----

Width W (Imperial)	0.5
--------------------	-----

Width W (Metric)	12.6
------------------	------

Bundle Diameter Min (Imperial)	0.98
--------------------------------	------

Bundle Diameter Min (Metric)	25.0
------------------------------	------

Bundle Diameter Max (Imperial)	5
--------------------------------	---

Bundle Diameter Max (Metric)	127.0
------------------------------	-------

Cable Tie Width Max (Imperial)	0.49
--------------------------------	------

Cable Tie Width Max (Metric)	12.5
------------------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)