

Specification Sheet

Part Number: T120RDH0K2



The tie contains a dual locking design to secure two bundles at once.

Head design can also provide spacing between parallel bundles.

Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66, Black, 50/pkg

Article Number	117-05501
Type	T120RDH
Color	Black (BK)
Quantity Per	pack
Product Description	The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Double-Head Cable Tie, 15.7" Long, 120lb Tensile Strength, PA66, Black, 50/pkg
Global Part Name	T120RDH-PA66-BK

Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	15.7
Length L (Metric)	398.0
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.3
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.18
Bundle Diameter Min (Metric)	4.6
Bundle Diameter Max (Imperial)	3.94
Bundle Diameter Max (Metric)	100
Bundle Diameter 1st Loop Max (Imperial)	4.0
Bundle Diameter 1st Loop Max (Metric)	101.6
Bundle Diameter 2nd Loop Max (Imperial)	2.0

Bundle Diameter 2nd Loop Max (Metric)	50.8
---------------------------------------	------

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
-------------------	------

Flammability	UL 94 V-2
--------------	-----------

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor and Outdoor Use
----------------	----------------------------

Operating Temperature	-40°F to +185°F (-40°C to +85°C)
-----------------------	----------------------------------

Reach Compliant (Article 33)	Yes
------------------------------	-----

ROHS Compliant	Yes
----------------	-----

Certification/Specification	UL-ZODZ2.E64139
-----------------------------	-----------------

UL Recognized (US)	Yes
--------------------	-----

UL Recognized (US and Canada)	Yes
-------------------------------	-----

Package Quantity (Imperial)	50
-----------------------------	----

Package Quantity (Metric)	50
---------------------------	----

Customs Number	3926909988
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)