

Specification Sheet

Part Number: 132-00010

 Product Image

Unique two piece tie allows parallel entry and exit through the head for easy assembly.  
PA66HIRHS material make it ideal for trucking and heavy equipment applications.

Button Head Cable Tie, 9.6” Long, 2.6” Max Bundle Diameter, 105lb, PA66HIRHSUV, Black, 50/pkg

|                     |                                                                                                                                                                                                                                                                                                                                                   |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 132-00010                                                                                                                                                                                                                                                                                                                                         |
| Type                | BT105R                                                                                                                                                                                                                                                                                                                                            |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                        |
| Quantity Per        | bag                                                                                                                                                                                                                                                                                                                                               |
| Product Description | The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping. |
| Short Description   | Button Head Cable Tie, 9.6” Long, 2.6” Max Bundle Diameter, 105lb, PA66HIRHSUV, Black, 50/pkg                                                                                                                                                                                                                                                     |

|                  |                       |
|------------------|-----------------------|
| Global Part Name | BT105R-PA66HIRHSUV-BK |
|------------------|-----------------------|

|                                     |       |
|-------------------------------------|-------|
| Minimum Tensile Strength (Imperial) | 105.0 |
|-------------------------------------|-------|

|                                   |       |
|-----------------------------------|-------|
| Minimum Tensile Strength (Metric) | 467.0 |
|-----------------------------------|-------|

|                     |     |
|---------------------|-----|
| Length L (Imperial) | 9.6 |
|---------------------|-----|

|                   |       |
|-------------------|-------|
| Length L (Metric) | 244.4 |
|-------------------|-------|

|                 |                |
|-----------------|----------------|
| Fixation Method | Connector Clip |
|-----------------|----------------|

|                               |      |
|-------------------------------|------|
| Identification Plate Position | none |
|-------------------------------|------|

|                    |    |
|--------------------|----|
| Releasable Closure | No |
|--------------------|----|

|             |              |
|-------------|--------------|
| Tie Closure | plastic pawl |
|-------------|--------------|

|         |                  |
|---------|------------------|
| Variant | Outside Serrated |
|---------|------------------|

|                    |     |
|--------------------|-----|
| Width W (Imperial) | 0.2 |
|--------------------|-----|

|                  |     |
|------------------|-----|
| Width W (Metric) | 5.6 |
|------------------|-----|

|                                |      |
|--------------------------------|------|
| Bundle Diameter Min (Imperial) | 0.25 |
|--------------------------------|------|

|                              |     |
|------------------------------|-----|
| Bundle Diameter Min (Metric) | 6.4 |
|------------------------------|-----|

|                                |     |
|--------------------------------|-----|
| Bundle Diameter Max (Imperial) | 2.6 |
|--------------------------------|-----|

|                              |      |
|------------------------------|------|
| Bundle Diameter Max (Metric) | 66.7 |
|------------------------------|------|

|                             |                                                                          |
|-----------------------------|--------------------------------------------------------------------------|
| Material                    | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Material Shortcut           | PA66HIRHSUV                                                              |
| Material Cable Tie          | Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)  |
| Material Head               | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) |
| Flammability                | UL 94 HB                                                                 |
| Operating Temperature       | -40°F to +221°F (-40°C to +105°C)                                        |
| Package Quantity (Imperial) | 50                                                                       |
| Package Quantity (Metric)   | 50                                                                       |
| Customs Number              | 3926909988                                                               |