

Specification Sheet

Part Number: 133-01478



- Angled channel allows specific guidance around corners or obstructions.
- U-Shape channel provides three sides of protection for wire or bundle.
- High-quality polypropylene material with high heat resistance.
- Protects against abrasion and other environmental factors.

Mini Channel, 3.53" Long, 45° Angle, Large, PPT20, Black, 900/pkg

Article Number	133-01478
Type	45MINICHNL2
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
Short Description	Mini Channel, 3.53" Long, 45° Angle, Large, PPT20, Black, 900/pkg
Global Part Name	45MINICHNL2-PPTD20-BK

Length L (Imperial)	3.53
Length L (Metric)	89.7
Variant	135°
Width W (Imperial)	0.06
Width W (Metric)	15.0
Height H (Imperial)	0.60
Height H (Metric)	15.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9

Material	Polypropylene 20% Talkum (PPTD20)
Material Shortcut	PPTD20
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	900
Package Quantity (Metric)	900
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)