

Specification Sheet

Part Number: 133-01480



L-Shape channel provides 2 sides of protection.

45-degree angle guides round bundles around curves and through space constrained areas.

Polypropylene material provides good chemical and heat resistance.

Mini Channel, 2.05" Long, 45° Angle, Small, PPT20, Black, 4000/pkg

Article Number	133-01480
----------------	-----------

Type	45MINICHNL
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton Mini Channels provide protection and configurable routing in a cost-effective wire management solution. The variety of sizes and configurations enables engineers and installers to create optimum routing scenarios. Mini channels replace engineered channels that are costly to design and develop.
---------------------	--

Short Description	Mini Channel, 2.05" Long, 45° Angle, Small, PPT20, Black, 4000/pkg
-------------------	--

Global Part Name	45MINICHNL-PPTD20-BK
------------------	----------------------

Length L (Imperial)	2.05
Length L (Metric)	52.0
Variant	135°
Width W (Imperial)	0.06
Width W (Metric)	10.0
Height H (Imperial)	0.39
Height H (Metric)	10.0
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9

Material	Polypropylene 20% Talkum (PPTD20)
Material Shortcut	PPTD20
Flammability	UL 94 HB
Halogen Free	Yes

UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)