

Specification Sheet

Part Number: 133-03187

Dual pipe clip secures two routings together while keeping them separated, to prevent chafing or heat transfer

Inverted retaining legs and narrow opening prevent inadvertent disengagement of pipe

Controlled flex and angled entry promote easy pipe installation

For use with routings of the following size:

2 x 65-70 mm



Tube and Pipe clip, 2x 6.5-7.0mm diameter, PA66HIRHSUV, Black, 3,000/ctn

Article Number	133-03187
----------------	-----------

Type	PC6.5X2
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.
---------------------	--

Short Description	Tube and Pipe clip, 2x 6.5-7.0mm diameter, PA66HIRHSUV, Black, 3,000/ctn
-------------------	--

Global Part Name	PC6.5X2-PA66HIRHSUV-BK
Length L (Imperial)	1.03
Length L (Metric)	25.25
Width W (Imperial)	0.4
Width W (Metric)	10.16
Height H (Imperial)	0.49
Height H (Metric)	12.0
Nominal Diameter (Metric)	6.35
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)