


Specification Sheet

Part Number: 133-04257



The different fastening orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters

Edge Clip and Tape Clip, Panel Thickness 0.06 - 0.08 ", 1.43" Long, PA66HIRHSUV, Black, 4000/ctn

Article Number	133-04257
----------------	-----------

Type	TEC70
------	-------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. These edge clips are molded to a tape bar, which can be secured to cables with cable ties or tape. The clip is easy to secure, and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.
---------------------	---

Short Description	Edge Clip and Tape Clip, Panel Thickness 0.06 - 0.08 ", 1.43" Long, PA66HIRHSUV, Black, 4000/ctn
-------------------	--

Global Part Name	TEC70-PA66HIRHSUV/MET-BK
------------------	--------------------------

Length L (Imperial)	0.61
---------------------	------

Length L (Metric)	15.5
-------------------	------

Offset Length (Imperial)	0.32
--------------------------	------

Offset Length (Metric)	8.1
------------------------	-----

Fixation Method	Edge Clip
-----------------	-----------

Width W (Imperial)	0.39
--------------------	------

Width W (Metric)	9.9
------------------	-----

Bundle Diameter Max (Imperial)	0.31
--------------------------------	------

Bundle Diameter Max (Metric)	7.8
------------------------------	-----

Height H (Imperial)	0.38
---------------------	------

Height H (Metric)	9.6
-------------------	-----

Diameter D (Imperial)	0.16
-----------------------	------

Diameter D (Metric)	4.0
---------------------	-----

Panel Thickness Min (Imperial)	0.06
--------------------------------	------

Panel Thickness Max (Imperial)	0.08
--------------------------------	------

Panel Thickness Min (Metric)	1.6
Panel Thickness Max (Metric)	2.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Metal (MET)
Material Shortcut	MET PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988