

Specification Sheet

Part Number: 133-03427



- Can be easily assembled to convoluted tubing and reliably remain in position
- Internal rib prevents movement or rattling
- Multiple configurations to mount to a variety of surfaces
- Releaseable to allow for maintenance

Conduit Clamps, Size 10, Mounting Hole 10.6 mm, Offset 40.5 mm, PA66, Black, 850/carton

Article Number	133-03427
Type	CDC10S40.5M10
Color	Black (BK)
Quantity Per	carton
Product Description	Conduit Clamps, Size 10, Mounting Hole 10.6 mm, Offset 40.5 mm, PA66, Black, 850/carton
Short Description	Conduit Clamps, Size 10, Mounting Hole 10.6 mm, Offset 40.5 mm, PA66, Black, 850/carton
Global Part Name	CDC10S40.5M10-PA66-BK

Length L (Imperial)	2.58
Length L (Metric)	65.5
Offset Length (Imperial)	1.59
Offset Length (Metric)	40.5
Fixation Method	screwable
Width W (Imperial)	0.9
Width W (Metric)	23
Bundle Diameter Max (Imperial)	0.39
Bundle Diameter Max (Metric)	10.0
Height H (Imperial)	2.0
Height H (Metric)	50.7
Diameter D (Imperial)	0.43
Diameter D (Metric)	11.0
Mounting Hole Diameter D (Imperial)	0.42 "
Mounting Hole Diameter D (Metric)	10.6 mm
Stud Diameter (Metric)	M10

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	850
Package Quantity (Metric)	850
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com