

Specification Sheet

Part Number: 148-00091



- Clamp provides low insertion and high extraction force.
- Various sizes available to accommodate all different sizes of bundles.
- Clamp can be installed both before and after installation of bundles.

Wire Clamping Cable Ties, Version B, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

Article Number	148-00091
Type	T50SOSWB4.3E
Color	Black (BK)
Quantity Per	pack
Product Description	Wire Clamping Cable Ties secure easily to wire frames for a tight fit and are available in four different wire frame sizes and two separate orientations to provide both perpendicular and parallel routing. The wire clamp design is ideally suited for easing the application process on the production floor by allowing for an easy snap fit of the harness assembly to the wire frame.
Short Description	Wire Clamping Cable Ties, Version B, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

Global Part Name	T50SOSWB4.3E-PA66HS-BK
------------------	------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	150.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.3
----------------------	-----

Diameter D (Imperial) 0.17

Nominal Diameter (Imperial) 0.19

Nominal Diameter (Metric) 4.3

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

UV Resistant (Yes/No) No

Use Conditions For Indoor and Outdoor Use

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 500

Package Quantity (Metric) 500

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)