

Specification Sheet

Part Number: 148-00092



Clamp provides low insertion and high extraction force.

Various sizes available to accommodate all different sizes of bundles.

Clamp can be installed both before and after installation of bundles.

Wire Clamping Cable Ties, Version A, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

Article Number

148-00092

Type

T50SOSWA4.3E

Color

Black (BK)

Quantity Per

pack

Product Description

Wire Clamping Cable Ties secure easily to wire frames for a tight fit and are available in four different wire frame sizes and two separate orientations to provide both perpendicular and parallel routing. The wire clamp design is ideally suited for easing the application process on the production floor by allowing for an easy snap fit of the harness assembly to the wire frame.

Short Description

Wire Clamping Cable Ties, Version A, Diameter Attachment .17", 6.0" Long, Black, PA66HS, 500/pkg

Global Part Name	T50SOSWA4.3E-PA66HS-BK
------------------	------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	150.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.06
--------------------------------	------

Bundle Diameter Min (Metric)	1.6
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.3
----------------------	-----

Diameter D (Imperial)	0.17
Nominal Diameter (Imperial)	0.19
Nominal Diameter (Metric)	4.3
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)