

Specification Sheet

Part Number: 148-90066

Quick release simplifies insertion and removal of wires for fast, safe and secure operation.

Connects solid and stranded wires within same housing for versatile wire management.

Accepts 12 AWG solid wire and 14 - 28 AWG stranded wire.

Clear housing eases inspection with visual verification that wires have been inserted properly.



HelaCon Releasable Wire Connector, 3-Port, (Piece & PA66), Clear, 500/pkg

Article Number	148-90066
----------------	-----------

Type	HCRN-3
------	--------

Color	Clear (CL)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HelaCon Releasable Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connections and distribution of cable and conductors in electrical installation applications. These connectors have a lever action that opens for insertion and repositioning of wires and snaps closed to establish a secure connection. Suitable for use with solid and stranded wires.
---------------------	--

Short Description	HelaCon Releasable Wire Connector, 3-Port, (Piece & PA66), Clear, 500/pkg
Global Part Name	HCRN-3-PC-CL
Length L (Imperial)	0.67
Length L (Metric)	17.0
Width W (Imperial)	0.81
Width W (Metric)	20.5
Height H (Imperial)	0.55
Height H (Metric)	14.0
Material	Polycarbonate (PC)
Material Shortcut	PC
Flammability	UL 94 V-0
Halogen Free	Yes
Use Conditions	For Indoor Use Only
Operating Temperature	-22°F to +185°F (-30°C to +85°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL UL 486C
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	8536908085

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)