

## Specification Sheet

Part Number: 148-90060

Quick release simplifies insertion and removal of wires for fast, safe and secure operation.

Connects solid and stranded wires within same housing for versatile wire management.

Accepts 12 AWG solid wire and 14 - 28 AWG stranded wire.

Clear housing eases inspection with visual verification that wires have been inserted properly.



HelaCon Releasable Wire Connector, 3-Port, (Piece & PA66), Clear, 50/pkg

|                |           |
|----------------|-----------|
| Article Number | 148-90060 |
|----------------|-----------|

|      |        |
|------|--------|
| Type | HCRN-3 |
|------|--------|

|       |            |
|-------|------------|
| Color | Clear (CL) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                          |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HelaCon Releasable Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connections and distribution of cable and conductors in electrical installation applications. These connectors have a lever action that opens for insertion and repositioning of wires and snaps closed to establish a secure connection. Suitable for use with solid and stranded wires. |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                       |                                                                          |
|-----------------------|--------------------------------------------------------------------------|
| Short Description     | HelaCon Releasable Wire Connector, 3-Port, (Piece & PA66), Clear, 50/pkg |
| Global Part Name      | HCRN-3-PC-CL                                                             |
| Length L (Imperial)   | 0.67                                                                     |
| Length L (Metric)     | 17.0                                                                     |
| Width W (Imperial)    | 0.81                                                                     |
| Width W (Metric)      | 20.5                                                                     |
| Height H (Imperial)   | 0.55                                                                     |
| Height H (Metric)     | 14.0                                                                     |
| Material              | Polycarbonate (PC)                                                       |
| Material Shortcut     | PC                                                                       |
| Flammability          | UL 94 V-0                                                                |
| Halogen Free          | Yes                                                                      |
| Use Conditions        | For Indoor Use Only                                                      |
| Operating Temperature | -22°F to +185°F (-30°C to +85°C)                                         |

|                              |              |
|------------------------------|--------------|
| Reach Compliant (Article 33) | Yes          |
| ROHS Compliant               | Yes          |
| Certification/Specification  | UL   UL 486C |
| UL Listed (US and Canada)    | Yes          |
| UL Listed (US)               | Yes          |
| Package Quantity (Imperial)  | 50           |
| Package Quantity (Metric)    | 50           |
| Customs Number               | 8536908085   |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)