

Specification Sheet

Part Number: MMB10C2



Masonry Mounts provide a permanent solution when fastening wire and cables to masonry surfaces.

The mounts have easy installation into predrilled holes allowing for faster use.

Masonry Cable Tie Mount, 1.712"L, 0.312" Hole Dia, 0.18" Max Cable Tie Width, PA66STHS, Black, 100/pkg

Article Number	151-00326
Type	MMB1
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton Masonry Mounts provide a permanent method of attaching wire and cable to masonry surfaces. Masonry mounts simply tap into predrilled holes and can be used for indoor and outdoor applications.
Short Description	Masonry Cable Tie Mount, 1.712"L, 0.312" Hole Dia, 0.18" Max Cable Tie Width, PA66STHS, Black, 100/pkg
Global Part Name	MMB1-PA66STHS-BK

Length L (Imperial)	1.712
Length L (Metric)	43.5
Fixation Method	Threaded bolt
Width W (Imperial)	0.508
Width W (Metric)	12.9
Cable Ties	T18 - T50
Height H (Imperial)	0.50
Height H (Metric)	12.70
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Mounting Hole Diameter D (Imperial)	0.312 "
Mounting Hole Diameter D (Metric)	8.0 mm
Mounting Hole Diameter D Max (Metric)	8.0
Material	Polyamide 6.6, super tough, heat stabilized (PA66STHS)
Material Shortcut	PA66STHS

Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)