

Specification Sheet

Part Number: LTM2500C2



The strap is parallel to the mount when inserted into the head, providing a fixed insertion point for the cable tie.

Lashing Tie Mount, 0.73 x 1.5", 0.25" Screw, PA66HS, Black, 100/pkg

Article Number	151-00358
----------------	-----------

Type	LTM250
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The lashing tie mount is designed to snap into the T250 lashing tie. The tie head is assembled perpendicular to the mount. The strap is parallel to the mount when inserted into the head. The lashing tie mount is recommended for indoor or outdoor wall mount cable applications.
---------------------	--

Short Description	Lashing Tie Mount, 0.73 x 1.5", 0.25" Screw, PA66HS, Black, 100/pkg
-------------------	---

Global Part Name	LTM250-PA66HS-BK
------------------	------------------

Length L (Imperial)	1.5
Length L (Metric)	37.1
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.73
Width W (Metric)	18.5
Cable Ties	T250
Height H (Imperial)	0.38
Height H (Metric)	9.6
Cable Tie Width Max (Imperial)	0.49
Cable Tie Width Max (Metric)	12.5
Mounting Hole Diameter D (Imperial)	0.26 "
Mounting Hole Diameter D (Metric)	6.6 mm
Mounting Hole Diameter D Max (Metric)	6.6
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com