

Specification Sheet

Part Number: 151-01404

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications.

Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.

HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Connector Clip with Bracket, 2.79" Long, PA66HIRHS, Natural, 1000/box

Article Number	151-01404
Type	BCBRKT55M
Color	Natural (NA)
Quantity Per	pack
Product Description	HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times.
Short Description	Connector Clip with Bracket, 2.79" Long, PA66HIRHS, Natural, 1000/box

Global Part Name	BCBRKT55M-PA66HIRHS-NA
Length L (Imperial)	2.79
Length L (Metric)	70.9
Offset Length (Imperial)	2.17
Offset Length (Metric)	55.15
Width W (Imperial)	1.97
Width W (Metric)	50.0
Height H (Imperial)	0.62
Height H (Metric)	15.8
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)