

Specification Sheet

Part Number: 151-01633


For use with HellermannTyton T18 - T150 cable ties to provide stability when securing bundles.

4-way opening allows cable ties to be installed parallel or perpendicular to bundles.

The high-heat, high-bond adhesive is ideal for outdoor applications, with a static load weight of 2.1 lb.

Two predrilled holes extend mounting options and solutions.

Extended adhesive liner is easy to remove quickly.



High Heat High Bond Acrylic Adhesive Base, 1.49 x 1.49", Use T18-T150 Tie, PA66HIRHSUV, Black, 100/pkg

Article Number	151-01633
----------------	-----------

Type	MB5A4
------	-------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	MB5A4 adhesive mounts are for use with HellermannTyton T18 - T150 Series cable ties to provide stability when securing bundles. The high-heat, high-bond acrylic adhesive-backed mounts can be used to secure a bundle and have two predrilled holes to extend mounting options.
---------------------	--

Short Description	High Heat High Bond Acrylic Adhesive Base, 1.49 x 1.49", Use T18-T150 Tie, PA66HIRHSUV, Black, 100/pkg
Global Part Name	MB5A4-PA66HIRHSUV-BK
Length L (Imperial)	1.49
Length L (Metric)	37.7
Fixation Method	Adhesive
Width W (Imperial)	1.49
Width W (Metric)	37.7
Cable Ties	T18 - T150
Height H (Imperial)	.28
Height H (Metric)	7.1
Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.9
Mounting Hole Diameter D (Imperial)	0.19 "
Mounting Hole Diameter D (Metric)	4.8 mm
Mounting Hole Centers (Imperial)	1

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Adhesive	Acrylic foam
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

