


Specification Sheet

Part Number: 151-01857

For use with HellermannTyton T18 - T150 or Wide Strap cable ties to provide stability when securing bundles.

The high-heat, high-bond adhesive is ideal for outdoor applications, with a static load weight of 2.1 lb.

Extended adhesive liner is easy to remove quickly.



High Heat High Bond Acrylic Adhesive Base, 1.5 x 1.5", Use T18-T150 or WideStrap Tie, PA66HIRHSUV, Bk, 100/pkg

Article Number	151-01857
Type	WSMB5AHB
Color	Black (BK)
Quantity Per	pack
Product Description	HellermannTyton's Wide Strap Adhesive Mount pairs with our exclusive line of Wide Strap Cable Ties and is ideal for extreme-duty applications. The mount features 3M™ VHB™ (Very High Bond) adhesive, which actually builds strength over time and holds securely to difficult materials such as aluminum, steel, plastics and painted and powder-coated surfaces.
Short Description	High Heat High Bond Acrylic Adhesive Base, 1.5 x 1.5", Use T18-T150 or WideStrap Tie, PA66HIRHSUV, Bk, 100/pkg

Global Part Name	WSMB5AHB-PA66HIRHSUV-BK
Length L (Imperial)	1.49
Length L (Metric)	37.7
Fixation Method	Adhesive
Width W (Imperial)	1.49
Width W (Metric)	37.7
Cable Ties	T18 - T150
Height H (Imperial)	.30
Height H (Metric)	7.7
Cable Tie Width Max (Imperial)	0.52
Cable Tie Width Max (Metric)	13.2
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Adhesive	Acrylic foam

Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com