

Specification Sheet

Part Number: 151-03102



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, 0.86 x .62", 0.25" Hole Dia, 0.31" Max Tie Width, PA666V0, Black, 100/pkg

Article Number	151-03102
----------------	-----------

Type	CTM4
------	------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.
---------------------	---

Short Description	Cable Tie Anchor Mount, 0.86 x .62", 0.25" Hole Dia, 0.31" Max Tie Width, PA666V0, Black, 100/pkg
-------------------	---

Global Part Name	CTM4-PA666V0-BK
------------------	-----------------

Length L (Imperial)	0.86
Length L (Metric)	21.8
Fixation Method	Screw Mount
Width W (Imperial)	0.62
Width W (Metric)	15.8
Cable Ties	T18 - T120
Height H (Imperial)	0.37
Height H (Metric)	9.4
Cable Tie Width Max (Imperial)	0.31
Cable Tie Width Max (Metric)	7.8
Mounting Hole Diameter D (Imperial)	0.25
Mounting Hole Diameter D (Metric)	6.4 mm
Mounting Hole Diameter D Max (Metric)	6.4
Material	Polyamide 6.6/6, V0 (PA666V0)
Material Shortcut	PA666V0

Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	ASTM E 662 Exova NFPA130: 2017 ASTM 1354 ASTM E 162
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com