

Specification Sheet

Part Number: 151-04027



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse, 360-degree rotation and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic Clip, Small, 1/2", Neodymium Magnet/POM/ST, 10lb Pull Force, Black, 10/bg

Article Number	151-04027
----------------	-----------

Type	MAGC10S
------	---------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Magnetic clips are designed to route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle by pushing it into the clip and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The clips are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.
---------------------	--

Short Description	Magnetic Clip, Small, ½", Neodymium Magnet/POM/ST, 10lb Pull Force, Black, 10/bg
Global Part Name	MAGC10S-NDFEB35M/POM/ST-BK
Length L (Imperial)	0.62
Length L (Metric)	15.8
Fixation Method	Magnet
Height H (Imperial)	0.73
Height H (Metric)	18.5
Depth D (Imperial)	0.15
Depth D (Metric)	3.9
Diameter D (Imperial)	0.75
Diameter D (Metric)	19
Material	Polyacetal (POM) Steel (ST) Neodymium alloy 35M (NDFEB35M)
Material Shortcut	ST POM NDFEB35M
Halogen Free	Yes

Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)