

Specification Sheet

Part Number: 151-04215

- Vertical slotted pocket design allows easier assembly and adjustability.
- Integrated retaining gap allows for single-tool tightening.
- Locating grooves create a visual reference point for easier sensor alignment.
- Multiple mounting slot positions for quick assembly and cable tie mount to manage excess cable loops.



Proximity Sensor Mount, Right Angle, 18 mm, M6, PPS/ST/ZN, Black, 1/bag

Article Number	151-04215
Type	SENMT18M6
Color	Black (BK)
Quantity Per	pack
Product Description	The sensor mount product family is a system of mounting, positioning and wire management devices designed for proximity sensors used on conveyors and industrial automation equipment. The unique retention slot feature quickly positions and retains the sensor locknut, which simplifies installation and repositioning. Hybrid construction with galvanized steel mounting plate reduces weight, tolerates high torque and adds stability. Attach with an M6 or #10 mounting screw.

Short Description	Proximity Sensor Mount, Right Angle, 18 mm, M6, PPS/ST/ZN, Black, 1/bag
Global Part Name	SENMT18M6-PPS/ST/ZN-BK
Length L (Imperial)	1.84
Length L (Metric)	45.7
Fixation Method	Screw Mounting
Width W (Imperial)	1.50
Width W (Metric)	38.0
Height H (Imperial)	1.87
Height H (Metric)	47.5
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.08
Mounting Hole Diameter D (Imperial)	0.16 "
Mounting Hole Diameter D (Metric)	4.3 mm
Material	Polyphenylene Sulfide (PPS) Steel (ST) Zinc plated (ZN)

Material Shortcut	ZN PPS ST
Flammability	UL 94 HB
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8302497500

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com