

Specification Sheet

Part Number: MB4SHA10C2



- For use with HellermannTyton T18 - T50 cable ties to provide stability when securing bundles.
- The rubber-based adhesive is an economical choice ideal for indoor applications, with a static load weight of 1.1 lb.
- A predrilled hole extends mounting options and solutions.
- Extended adhesive liner is easy to remove quickly.

Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg

Article Number	151-29203
Type	MB4SHA
Color	White (WH)
Quantity Per	pack
Product Description	MB4SHA adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have a predrilled hole to extend mounting options.
Short Description	Rubber Adhesive Cable Tie Mount, 1.12 x 1.12", Use With T18-T50 Cable Tie, PA66, White, 100/pkg

Global Part Name	MB4SHA-PA66-WH
------------------	----------------

Length L (Imperial)	1.12
---------------------	------

Length L (Metric)	28.3
-------------------	------

Fixation Method	Adhesive
-----------------	----------

Width W (Imperial)	1.12
--------------------	------

Width W (Metric)	28.3
------------------	------

Cable Ties	T18 - T50
------------	-----------

Height H (Imperial)	.23
---------------------	-----

Height H (Metric)	5.8
-------------------	-----

Cable Tie Width Max (Imperial)	0.18
--------------------------------	------

Cable Tie Width Max (Metric)	4.6
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.15 "
-------------------------------------	--------

Mounting Hole Diameter D (Metric)	3.9 mm
-----------------------------------	--------

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
-------------------	------

Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Adhesive Operating Temperature	0°F to +150°F (-18 °C to +66 °C)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com