

Specification Sheet

Part Number: 151-01153



Clip can be installed by hand – no need for hardware or tools.

Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.4" Long, 0.02 - 0.24" Panel Thickness, PA66HIRHS, Natural, 4000/box

Article Number	151-01153
----------------	-----------

Type	SOC9FT6
------	---------

Color	Natural (NA)
-------	--------------

Quantity Per	pack
--------------	------

Product Description	Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.
---------------------	---

Short Description	Standoff Bundling Clip, 1.4" Long, 0.02 - 0.24" Panel Thickness, PA66HIRHS, Natural, 4000/box
-------------------	---

Global Part Name	SOC9FT6-PA66HIRHS-NA
------------------	----------------------

Length L (Imperial)	1.4
---------------------	-----

Length L (Metric)	35.5
-------------------	------

Offset Length (Imperial)	0.8
--------------------------	-----

Offset Length (Metric)	20.3
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	1.1
--------------------	-----

Width W (Metric)	27.95
------------------	-------

Height H (Imperial)	0.47
---------------------	------

Height H (Metric)	11.94
-------------------	-------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.24
--------------------------------	------

Panel Thickness Min (Metric)	0.5
------------------------------	-----

Panel Thickness Max (Metric)	6.1
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
-------------------------------------	---------------

Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
-----------------------------------	--------------

Mounting Hole Diameter D Min (Imperial) 0.24

Mounting Hole Diameter D Max (Imperial) 0.27

Mounting Hole Diameter D Max (Metric) 6.9

Material Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL 94 HB

UV Resistant (Yes/No) No

Use Conditions For Indoor Use Only

Operating Temperature -40°F to +221°F (-40°C to +105°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 4000

Package Quantity (Metric) 4000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)