

Specification Sheet

Part Number: 151-01249



Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.

Connector Clip with Bracket, 2.06" Long, PA66HIRHSUV, Black, 3000/pkg

Article Number	151-01249
----------------	-----------

Type	CC90BRKT
------	----------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip with Bracket, 2.06" Long, PA66HIRHSUV, Black, 3000/pkg
-------------------	---

Global Part Name	CC90BRKT-PA66HIRHSUV-BK
Length L (Imperial)	2.2
Length L (Metric)	108.4
Width W (Imperial)	2.06
Width W (Metric)	53.0
Height H (Imperial)	2.2
Height H (Metric)	10.9
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)