Specification Sheet

Part Number: 151-01769

Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.

Controlled flex and angled entry promote easy installation.

Non-rotating fir tree demonstrates easy insertion with high extraction resistance.

MOC Clip, 14 mm, with 4 x Oval Fir Tree, PA66HIRHSUV, Black, 3000/ctn

Article Number	151-01769
Type	MOC14FTOVAL
Color	Black (BK)
Quantity Per	pack
Product Description	The MOC with Oval Fir Tree features HellermannTyton's unique retention clip attached to a 4x oval fir tree that will not rotate in the mounting hole. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point against a panel. This one design exceeds automotive requirements for the four most common oval sizes: 6.2x12.2 mm, 6.5x12.5 mm, 6.5x13 mm and 7x12 mm.
Short Description	MOC Clip, 14 mm, with 4 x Oval Fir Tree, PA66HIRHSUV, Black, 3000/ctn

Global Part Name	MOC14FTOVAL-PA66HIRHSUV-BK
Length L (Imperial)	0.93
Length L (Metric)	23.6
Fixation Method	Fir Tree
Bundle Diameter Min (Imperial)	0.53
Bundle Diameter Min (Metric)	13.5
Bundle Diameter Max (Imperial)	0.62
Bundle Diameter Max (Metric)	15.8
Height H (Imperial)	1.61
Height H (Metric)	40.9
Depth D (Imperial)	0.39
Depth D (Metric)	10.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75

Mounting Hole Diameter D (Imperial)	0.26 x 0.51 " 0.27" x 0.47 " 0.24 x 0.48 " 0.28 x 0.47 " 0.26 x 0.49 "
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm 7.0 x 12.0 mm 6.5 x 12.5 mm 6.2 x 12.2 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.