

Specification Sheet

Part Number: 151-02802



Connector clip designed to meet USCAR EWCAP-005-7 clip slot specifications, assuring compliance.

Meets installation and extraction requirements of SAE/USCAR-2, for ease of insertion and reliable performance.

Offset design allows for clearance from obstructions and sheet metal contours.

Connector Clip with Offset M10 Thread Stud Mount, 28mm Offset, 7mm Conn Clip, PA66HIRHSUV, BK, 2000/ctn

Article Number	151-02802
----------------	-----------

Type	CCM10SO28R
------	------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip with Offset M10 Thread Stud Mount, 28mm Offset, 7mm Conn Clip, PA66HIRHSUV, BK, 2000/ctn
-------------------	---

Global Part Name	CCM10SO28R-PA66HIRHSUV-BK
Length L (Imperial)	1.53
Length L (Metric)	38.9
Offset Length (Imperial)	1.102
Offset Length (Metric)	28.0
Fixation Method	Stud Mount
Variant	M10 Threaded Stud 28 mm Offset
Height H (Imperial)	0.736
Height H (Metric)	18.7
Stud Diameter (Metric)	M10
Stud Diamater (Imperial)	0.3937
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes

Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)