

Specification Sheet

Part Number: 151-03550

Smaller footprint for applications where space is constrained.

Attach using a bolt in an existing threaded hole, or bolt and nut for a non-threaded hole, for versatile mounting options.

One-piece ratchet closure allows for fast and easy installation.

Clamp interior is designed to guide and center bundles to reduce pinching.



M6 Bolt Mount Ratchet Clamp, Low Torque, 0.76 - 1.42" Bundle, PA66HIRHSUV, BK, 150/bg

Article Number	151-03550
Type	CMRCCLM6
Color	Black (BK)
Quantity Per	pack

Product Description	The Bolt Mount Ratchet Clamp offers versatility when managing conduit, wires, cables and hoses. It is specially designed for locations with space constraints or where offset mounting options are not ideal. Available with a compression limiter for crush resistance in high-torque applications, or in all-plastic for low- to medium-torque applications. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal or addition of cables simply by inserting a flat-head screwdriver. In this way, the clamp can be reused without removing it from the mounting surface.
Short Description	M6 Bolt Mount Ratchet Clamp, Low Torque, 0.76 - 1.42" Bundle, PA66HIRHSUV, BK, 150/bg
Global Part Name	CMRCCLM6-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	250
Minimum Tensile Strength (Metric)	1112
Length L (Imperial)	4.93
Length L (Metric)	125.3
Fixation Method	Screw Mount
Width W (Imperial)	1.38
Width W (Metric)	35.1
Bundle Diameter Min (Imperial)	0.76
Bundle Diameter Min (Metric)	19.3

Bundle Diameter Max (Imperial)	1.42
Bundle Diameter Max (Metric)	36.1
Height H (Imperial)	1.20
Height H (Metric)	30.4
Diameter D (Imperial)	0.25
Diameter D (Metric)	6.3
Bolt Size	0.236 "
Mounting Hole Diameter D (Imperial)	0.248 "
Mounting Hole Diameter D (Metric)	6.3 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use

Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	150
Package Quantity (Metric)	150
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)