

Specification Sheet

Part Number: 151-04022



No drilling or extra hardware required – just position on steel surface.

Magnetic mounts are reliable even in debris, dirt and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without leaving residue behind.

Magnetic Cable Tie Mount, Small, 0.75" Dia, Neodymium Magnet/POM/ST, 10lb Pull Force, White, 100/bg

Article Number	151-04022
Type	MAGCTM10S
Color	White (WH)
Quantity Per	pack

Product Description	Magnetic cable tie mounts route bundles by securing to steel surfaces without the need for a mounting hole. Simply attach the wire bundle to the mount with a cable tie and position it onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts. Magnetic cable tie mounts can be paired with standard T18-T50 cable ties.
Short Description	Magnetic Cable Tie Mount, Small, 0.75" Dia, Neodymium Magnet/POM/ST, 10lb Pull Force, White, 100/bg
Global Part Name	MAGCTM10S-NDFEB35M/POM/ST-WH
Fixation Method	Magnet
Height H (Imperial)	0.41
Height H (Metric)	10.5
Diameter D (Imperial)	0.75
Diameter D (Metric)	19
Cable Tie Width Max (Imperial)	0.23
Cable Tie Width Max (Metric)	5.9
Material	Steel (ST) Polyacetal (POM) Neodymium alloy 35M (NDFEB35M)

Material Shortcut	ST POM NDFEB35M
Halogen Free	Yes
Use Conditions	For Indoor Use Only
Plenum Rating	AH-2
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	8505110070

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com