

Specification Sheet

Part Number: 151-04156



Saddle Mounts are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate or standard cross-section cable ties.

Built-in CutZone safety feature prevents damage to wires and cables.

Unique EZ Feed slot maintains clear space to insert cable ties.

Allows flexibility of frame size and mounting location with #10 (M5) screw into panel surface or with T-nut in frame.

Article Number	151-04156
Type	CTSM3CZS
Color	Black (BK)
Quantity Per	bag
Product Description	Designed specifically for holding heavier cable bundles, these mounting bases can be used in many industries from agriculture to truck manufacturing. They mount securely and can be used with a wide variety of heavy duty cable ties up to 8.3 mm in width. Cables are held in place and aligned by troughs in the mount's arms. The EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Short Description	Cable Tie Saddle Mount, 1.1 x 0.66", 0.2" Hole Dia, 0.33" Max Tie Width, PA66HS, Black, 100/bag
Global Part Name	CTSM3CZS-PA66HS-BK
Length L (Imperial)	1.1
Length L (Metric)	28.0
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.66
Width W (Metric)	16.8
Height H (Imperial)	0.46
Height H (Metric)	11.7
Cable Tie Width Max (Imperial)	0.33
Cable Tie Width Max (Metric)	8.4
Mounting Hole Diameter D (Imperial)	0.21 "
Mounting Hole Diameter D (Metric)	5.35 mm
Material	Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com