

DRAWING No.  
152081

SHT. 1  
OF  
1 SHTS.

© THE COPYRIGHT OF THIS DRAWING IS RESERVED  
BY HELLERMANN TYTON. IT IS ISSUED ON CONDITION  
THAT IT IS NOT COPIED, REPRODUCED OR DISCLOSED  
TO A THIRD PARTY EITHER WHOLLY OR IN PART  
WITHOUT THE CONSENT IN WRITING OF HELLERMANN TYTON.

THIRD ANGLE PROJECTION

BS 8888

DO NOT SCALE  
IF IN DOUBT ASK

Q.A.

H/S Q.A.

H/S PROD

H/S SETT

REL. INSP.

EXT.ISS.CODE

12

STANDARD PART (AFTER UNRESTRICTED RECOVERY)

Technical drawing of a standard part after unrestricted recovery. The drawing shows a central horizontal section with two angled legs extending from it. Dimensions include P (total length), S (leg length), R (radius), Jw (leg width), Kw (leg width), Lw (leg width), and diameters ØH, ØJ, ØK, and ØL. A 45° angle is indicated for the legs. The part is labeled 573H534.

EXPANDED (AS SUPPLIED)

THE LENGTH OF EACH LEG MUST  
BE WITHIN 3.8 (.15) OF EACH OTHER

Technical drawing of the expanded part as supplied. It shows a rectangular part with dimensions p (length), h (height), j (width), k (width), and l (width). Diameters Øh, Øj, Øk, and Øl are also indicated. The part is labeled SECTION AA.

ADHESIVE COATING,  
EACH END, WHEN SPECIFIED

| PART NO.     | EXPANDED DIMENSIONS (AS SUPPLIED) |                |                            | RECOVERED DIAMETERS |               | RECOVERED DIMENSIONS |                |                 |              |
|--------------|-----------------------------------|----------------|----------------------------|---------------------|---------------|----------------------|----------------|-----------------|--------------|
|              | Øh                                | Øj,k,l         | p                          | ØH                  | ØJ,K,L        | P                    | R              | S               | Hw,Jw,Kw,Lw  |
|              | MIN                               | MIN            | TOL                        | MAX                 | MAX           | NOM                  | ±15%           | NOM             | NOM          |
| 573H534-*    | 60.2<br>(2.37)                    | 36.1<br>(1.42) | 152.4 ±15.2<br>(6.00 ±.60) | 20.1<br>(.79)       | 20.1<br>(.79) | 207.3<br>(8.16)      | 63.5<br>(2.50) | 103.6<br>(4.08) | 1.5<br>(.06) |
| 573H534-8    | 60.2<br>(2.37)                    | 36.1<br>(1.42) | 138.7 ±15.2<br>(5.46 ±.60) | 20.1<br>(.79)       | 20.1<br>(.79) | 207.3<br>(8.16)      | 63.5<br>(2.50) | 103.6<br>(4.08) | 1.5<br>(.06) |
| 573H534-*-01 | 60.2<br>(2.37)                    | 36.1<br>(1.42) | 90.9 ±10.2<br>(3.58 ±.40)  | 20.1<br>(.79)       | 20.1<br>(.79) | 135.6<br>(5.34)      | 27.7<br>(1.09) | 67.8<br>(2.67)  | 1.5<br>(.06) |

\* ALL MATERIAL CODES UNLESS OTHERWISE SPECIFIED.

NOTE : Hw, Jw, Kw AND Lw APPLIES TO 80% OF THE CIRCUMFERENCE ONLY.

4

P1591

CM

04/10/17

3

P1327

DC

06/10/10

2

P1304

DNH

09/02/10

1

P1194

S.Almond

02/04/08

ISSUE

NOTE No.

DRAWN

DATE

HellermannTyton

William Prance Road,  
Plymouth International Med. & Tech. Park,  
Plymouth, PL6 5WR  
Tel ++44 (0) 1752 701261  
Fax ++44 (0) 1752 790058

NAME

S.Almond

SCALE

NTS

ADHESIVE

DATE

02/04/08

DIMS IN

mm (in)

PART No.

573H534

TITLE

TRANSITION 3 TO 1

DRAWING No.

152081

A3

ORIGINAL SHEET SIZE  
420mm × 297mm

SHT. 1  
OF  
1 SHTS.