

## Specification Sheet

Part Number: FC2.2H4



Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable.

Releasable for easy access to cables when necessary.

Flat Ribbon Clamp, 2.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 500/pkg

|                |           |
|----------------|-----------|
| Article Number | 154-00014 |
|----------------|-----------|

|      |       |
|------|-------|
| Type | FC2.2 |
|------|-------|

|       |           |
|-------|-----------|
| Color | Gray (GY) |
|-------|-----------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                      |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary. |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                               |
|-------------------|-------------------------------------------------------------------------------|
| Short Description | Flat Ribbon Clamp, 2.2" Max Cable Width, 0.156" Hole Dia, PA66, Gray, 500/pkg |
|-------------------|-------------------------------------------------------------------------------|

|                                       |                      |
|---------------------------------------|----------------------|
| Global Part Name                      | FC2.2-PA66-GY        |
| Length L (Imperial)                   | 1.5                  |
| Length L (Metric)                     | 38.1                 |
| Width W (Imperial)                    | 2.5                  |
| Width W (Metric)                      | 63.5                 |
| Height H (Imperial)                   | 0.51                 |
| Height H (Metric)                     | 12.95                |
| Mounting Hole Diameter D (Imperial)   | 0.156 "              |
| Mounting Hole Diameter D (Metric)     | 4.0 mm               |
| Mounting Hole Diameter D Max (Metric) | 4.0                  |
| Material                              | Polyamide 6.6 (PA66) |
| Material Shortcut                     | PA66                 |
| Flammability                          | UL 94 V-2            |
| UV Resistant (Yes/No)                 | No                   |
| Use Conditions                        | For Indoor Use Only  |

|                              |                                  |
|------------------------------|----------------------------------|
| Operating Temperature        | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes                              |
| ROHS Compliant               | Yes                              |
| Package Quantity (Imperial)  | 500                              |
| Package Quantity (Metric)    | 500                              |
| Customs Number               | 3926909988                       |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)